Chemical Resistance RAFIX 30 FS⁺



Publication date: April 26, 2021

Chemicals	Resistance
Acetone	(+)
Biodiesel	(+)
Brake fluid DOT4	(++)
Diesel	(+)
H ₂ O ₂ 10%	(++)
Honing oil Castrol 981	(++)
Isopropyl alcohol	(++)
Cold cleaner	(+)
Linseed oil	(++)
Motor oil	(++)
Sodium hydroxide 10%	(++)
Rapeseed oil	(++)
Cleaning gasoline	(+)
Hydrochloric acid 10%	(++)
Forming Oil	(++)
Glass cleaner	(++)
Spiritus	(+)
Super gasoline ROZ 95	(+)

Explanation of signs

- ++ Resistant
- + Application-specific testing is recommended
- Not Resistant

Test conditions

Room temperature; storage period 120h; tested from the front side; testing acc. DIN ISO 16750-5

Important notice

Due to the diversity of the media, it is generally recommended to test always application-specific.

The information in this sheet only contains general descriptions and / or performance features, which may not apply precisely as described to the respective application, and which my change due to further product enhancements. The technical data, illustrations and other information about our products are the mere results of individual technical testing. These descriptions and other product features are only binding if they expressly agreed upon at the time of the conclusion of a binding contract. In all other cases, we reserve the right to make technical changes as well as changes of availability. Pictures and other graphic illustrations are approximations only. All product names may be trademarks or brand names of the RAFI Group or any other sub-supplier of RAFI. The use of such by any third parties for their own purposes may infringe the rights of the respective entity holding those rights. Subject to change and errors excepted. Details about delivery times and availability are noncommittal and have no legal force.